

# Quick Start Guide

## USB Type-C™ to Mini DisplayPort Adapter – Aluminum

Model: U444-06N-MDP-AL

Este guía esta disponible en español en la  
página de Tripp Lite: [www.tripplite.com/support](http://www.tripplite.com/support)

Ce guide est disponible en français sur le site Web de  
Tripp Lite : [www.tripplite.com/support](http://www.tripplite.com/support)

Русскоязычная версия настоящего краткого  
руководства представлена на веб-сайте компании  
Tripp Lite по адресу: [www.tripplite.com/support](http://www.tripplite.com/support)

### PROTECT YOUR INVESTMENT!

Register your product for quicker service and ultimate  
peace of mind. You could also win an ISOBAR6ULTRA  
surge protector—a \$100 value!

[www.tripplite.com/warranty](http://www.tripplite.com/warranty)



**TRIPP·LITE**



1111 W. 35th Street, Chicago, IL 60609 USA  
[www.tripplite.com/support](http://www.tripplite.com/support)

Copyright © 2019 Tripp Lite. All rights reserved.

## Product Features

- Supports USB DisplayPort 1.2 Alternate Mode for connecting a Mini DisplayPort monitor to a USB Type-C™ or Thunderbolt™ 3 port
- Supports Ultra High Definition (UHD) 4K x 2K video resolutions up to 3840 x 2160 (60 Hz)
- Supports up to 48-bit Deep Color (16 bits per channel)
- Supports 4:4:4 chroma subsampling
- Supports per lane data transfer rates of 5.4 Gbps (HBR2), 2.7 Gbps (HBR) and 1.62 Gbps (RBR)
- Compatible with HDCP 2.2
- Compact and lightweight aluminum housing fits easily into a backpack or laptop bag
- Plug-and-Play adapter—no software or drivers required

\*USB Type-C™ and USB-C™ are trademarks of USB Implementers Forum

## Package Contents

- U444-06N-MDP-AL
- Quick Start Guide

## System Requirements

- USB Type-C device that supports USB DisplayPort 1.2 Alternate Mode
- Mini DisplayPort monitor

## Installation

- 1.** Connect the adapter's USB Type-C connector to the USB Type-C or Thunderbolt 3 port on your smartphone, tablet, laptop or computer.

**Note:** *The U444-06N-MDP-AL can transfer only DisplayPort signals and is not compatible with Thunderbolt 3 or Thunderbolt 2 standards.*

- 2.** Using a Mini DisplayPort cable (such as Tripp Lite P584-Series cables), connect the adapter's Mini DisplayPort to a monitor.
- 3.** The video image will appear on the add-on monitor. Customize how video is displayed on the add-on monitor using your device's display settings.

# Specifications

<b>Connectors</b>	
USB	USB Type-C (Male)
DisplayPort	Mini DisplayPort (Female)
<b>Video</b>	
Maximum Resolution	3840 x 2160 (60 Hz)
Color Depth	48-bit Deep Color (16 bits per channel)
<b>Environmental</b>	
Operating Temperature	32 to 113°F (0 to 45°C)
Operating Humidity	10% to 85% RH, Non-Condensing
Storage Temperature	14 to 158°F (-10 to 70°C)
Storage Humidity	5% to 90% RH, Non-Condensing
<b>Power Requirements</b>	
Power Source	Bus Power

# Warranty and Product Registration

## 3-Year Limited Warranty

Tripp Lite warrants its products to be free from defects in materials and workmanship for a period of three (3) years from the date of initial purchase. Tripp Lite's obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. To obtain service under this warranty, you must obtain a Returned Material Authorization (RMA) number from Tripp Lite or an authorized Tripp Lite service center. Products must be returned to Tripp Lite or an authorized Tripp Lite service center with transportation charges prepaid and must be accompanied by a brief description of the problem encountered and proof of date and place of purchase. This warranty does not apply to equipment, which has been damaged by accident, negligence or misapplication or has been altered or modified in any way.

EXCEPT AS PROVIDED HEREIN, Tripp Lite MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Some states do not permit limitation or exclusion of implied warranties; therefore, the aforesaid limitation(s) or exclusion(s) may not apply to the purchaser.

## Warranty and Product Registration

EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL Tripp Lite BE LIABLE FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, Tripp Lite is not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or otherwise.

### Product Registration

Visit [www.tripplite.com/warranty](http://www.tripplite.com/warranty) today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!\*

\* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.





**1111 W. 35th Street, Chicago, IL 60609 USA**  
**[www.tripplite.com/support](http://www.tripplite.com/support)**