

Installation Guide

24-Port Cat6a Dual IDC STP High-Density 0.5U Patch Panel

Model: N252A-024-HUSHK

Este guía esta disponible en español en la página de Tripp Lite:
triplite.com/support

Ce guide est disponible en français sur le site Web de Tripp Lite :
triplite.com/support

Русскоязычная версия настоящего краткого руководства
представлена на веб-сайте компании Tripp Lite по адресу:
triplite.com/support

WARRANTY REGISTRATION

Register your product today and be
automatically entered to win an ISOBAR
surge protector in our monthly drawing!

triplite.com/warranty



1111 W. 35th Street, Chicago, IL 60609 USA • triplite.com/support

Copyright © 2019 Tripp Lite. All rights reserved.

Installation

1 Prepare Cables.


S/FTP Cable



Remove approximately 5 cm of cable sheath.



Roll the exposed braid back along the cable sheath.



Where a foil screen is present, remove approximately 2 mm of the exposed length.



Separate the conductors.


F/FTP Cable




Remove approximately 5 cm of cable sheath.



Roll the exposed foil back along the cable sheath.




Where a foil screen is present, remove approximately 2 mm of the exposed length.



Wrap the drain wire at least twice around the foil. Separate the conductors.

Installation

- 2 Seat each wire into the IDC slots according to the color scheme map. Punch down with a proper impact tool.




Installation

- 3 Use nylon cable ties to secure the bulk cables to the cable manager.

Cut off all excess straps.

Note: Do not over-tighten the cables.



Installation

- 4 Close the top of the panel and secure by tightening the side screws.



Installation

- 5 Attach the panel's grounding lug to a rack or cabinet.



Warranty and Product Registration

Lifetime Limited Warranty

Tripp Lite warrants its products to be free from defects in materials and workmanship for life. Tripp Lite's obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. To obtain service under this warranty, you must obtain a Returned Material Authorization (RMA) number from Tripp Lite or an authorized Tripp Lite service center. Products must be returned to Tripp Lite or an authorized Tripp Lite service center with transportation charges prepaid and must be accompanied by a brief description of the problem encountered and proof of date and place of purchase. This warranty does not apply to equipment, which has been damaged by accident, negligence or misapplication or has been altered or modified in any way.

EXCEPT AS PROVIDED HEREIN, Tripp Lite MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Some states do not permit limitation or exclusion of implied warranties; therefore, the aforesaid limitation(s) or exclusion(s) may not apply to the purchaser.

EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL Tripp Lite BE LIABLE FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, Tripp Lite is not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or otherwise.

Product Registration

Visit tripplite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!*

* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.



1111 W. 35th Street, Chicago, IL 60609 USA • www.tripplite.com/support