

Owner's Manual

USB-C[®] Mobile Dock and Multiport Adapter, 8K HDMI, 100W USB Charging

Model: U442-DOCK40-5

*USB Type-C[®] and USB-C[®] are registered trademarks
of USB Implementers Forum*

Este manual está disponible en español en la página
de Tripp Lite: tripplite.com

Ce manuel est disponible en français sur le site Web
de Tripp Lite : tripplite.com

Русскоязычная версия настоящего руководства
представлена на веб-сайте компании Tripp Lite по
адресу: tripplite.com

Dieses Handbuch ist in deutscher Sprache auf der
Tripp Lite-Website verfügbar: tripplite.com

WARRANTY REGISTRATION

Register your product today and be automatically entered
to win an ISOBAR[®] surge protector in our monthly drawing!

tripplite.com/warranty



1111 W. 35th Street, Chicago, IL 60609 USA
tripplite.com/support

Copyright © 2023 Tripp Lite. All rights reserved.

Product Features

- Transmit up to 8K video to an HDMI display from a USB-C host, connect and charge USB peripherals and charge the host PC via a 100W PD Charging port
- Compatible with laptops, computers and other USB Type-C host devices that support DisplayPort Alternate Mode
- HDMI port supports video resolutions up to 7680 x 4320 (8K) @ 30 Hz with High Dynamic Range (HDR10+) and HDCP 2.3 and below
- USB-A ports support USB 3.2 Gen 2 data transfer rates up to 10 Gbps
- One USB-A port provides up to 5V 1.5A (7.5W) charging while the other two ports provide 5V 0.9A (4.5W) to connected devices
- USB-C charging port supports PD 3.0 (100W), with 15W dedicated to powering the unit and 85W allocated to charging the host device
- All USB ports support over-current and short-circuit protection
- Thin profile design fits easily inside a small bag, purse or pocket

Package Includes

- U442-DOCK40-5
- Owner's Manual

Optional Accessories

- U040-C03-C – USB 2.0 Type-C to Type-C Cable, 3A, USB-IF Certified, 3 ft. (0.9m)
- U038-010-GY-MAX – USB 2.0 Type-A to Type-C Cable, UHMWPE and Aramid Fibers, 10 ft. (3m)
- P568-XXX-8K6 – 8K HDMI Cables

Instructions

1. Plug the dock's USB-C connector into the USB-C port of a compatible laptop, PC or other host device.

Note: The host device must support DisplayPort Alt Mode to transmit video via the HDMI port.

2. Connect the HDMI port on the dock to the HDMI port on a display using an HDMI cable (such as Tripp Lite's P568-XXX-8K6 Series, sold separately).
3. Connect and/or charge a device such as a mouse, keyboard, mobile phone etc. to the USB-A ports on the dock.
4. Charge the host device by connecting a USB-C cable to the USB-C PD charging port on the dock and into a USB-C power adapter.
5. Turn on the power to all connected devices. Video from the USB-C source should begin transmitting on the connected display.

Specifications

Connectors	
Input	USB-C (Male)
Output 1	USB-C (Female)
Output 2	USB-A (Female)
Output 3	USB-A (Female)
Output 4	USB-A (Female)
Output 5	HDMI (Female)
Charging	
USB-C	PD 3.0 (100W: 15W dedicated to powering unit and remaining 85W to host device)
USB-A (x1)	5V 1.5A (7.5W)
USB-A (x2)	5V 0.9A (4.5W)
Video	
HDMI	7680 x 4320 @ 30 Hz
Physical	
Unit Dimensions (HxWxL)	0.71 x 1.2 x 5.59 in. (1.8 x 3.05 x 1.42 cm)
Operating Temperature Range	32 to 113°F (0 to 45°C)
Storage Temperature Range	50 to 158°F (-10 to 70°C)
Operating Humidity Range	10% to 85% RH
Storage Humidity Range	5% to 90% RH

Warranty and Product Registration

1-Year Limited Warranty

Tripp Lite warrants its products to be free from defects in materials and workmanship for a period of three (3) years from the date of initial purchase. Tripp Lite's obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. To obtain service under this warranty, you must obtain a Returned Material Authorization (RMA) number from Tripp Lite or an authorized Tripp Lite service center. Products must be returned to Tripp Lite or an authorized Tripp Lite service center with transportation charges prepaid and must be accompanied by a brief description of the problem encountered and proof of date and place of purchase. This warranty does not apply to equipment, which has been damaged by accident, negligence or misapplication or has been altered or modified in any way.

EXCEPT AS PROVIDED HEREIN, Tripp Lite MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Some states do not permit limitation or exclusion of implied warranties; therefore, the aforesaid limitation(s) or exclusion(s) may not apply to the purchaser.

EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL Tripp Lite BE LIABLE FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, Tripp Lite is not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or otherwise.

PRODUCT REGISTRATION

Visit tripplite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!

** No purchase necessary. Void where prohibited. Some restrictions apply. Open to U.S. residents only. See tripplite.com for details.

Warranty and Product Registration

FCC Notice, Class B

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Any changes or modifications to this equipment not expressly approved by Tripp Lite could void the user's authority to operate this equipment.

Warranty and Product Registration

WEEE Compliance Information for Tripp Lite Customers and Recyclers (European Union)



Under the Waste Electrical and Electronic Equipment (WEEE) Directive and implementing regulations, when customers buy new electrical and electronic equipment from Tripp Lite they are entitled to:

- Send old equipment for recycling on a one-for-one, like-for-like basis (this varies depending on the country)
- Send the new equipment back for recycling when this ultimately becomes waste

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.



1111 W. 35th Street, Chicago, IL 60609 USA
triplite.com/support